

Digital acoustofluidics: contactless liquid handling device via acoustic streaming

Value Proposition

For decades, scientists have pursued the goal of performing automated reactions in a compact fluid processor with minimal human intervention. Digital microfluidics (DMF) pioneers an appealing solution for economical automation by programmable manipulation of nano- to pico-liter droplets on a miniaturized chip using electro-wetting forces.

Although numerous liquid handling techniques technologies (e.g., microfluidic chips and micro-well plates) have been developed, they generally rely on physical contact with a solid structure in order to contain, transport, or manipulate liquid reagents. This leads to the lack of fluid rewritability, and the associated benefits of multi-path routing and re-programmability, due to surface-adsorption-induced contamination on contacting structures. In addition, most current platforms are based on disposable, on-time use devices. Those features greatly limits the processing-speed, integration-scale, and complexity of reaction logics for liquid handling on a same device.

Technology

The present invention describes a system of unique contactless droplet-processing technique, Digital Acoustofluidics (DAF), which can digitally manipulate aqueous droplets (from 1nL to 100 μ L volumes) floating on a denser fluorinert oil horizontally *via* acoustic-streaming-induced hydrodynamic traps. These droplets are floating on an inert, immiscible layer of oil that effectively isolates the droplet above a solid surface that is custom patterned with an array of ultrasonic transducers.

DAF performed a three-stage cascade reaction protocol to rapidly detect enolase activity. Six aqueous droplets containing different reagents are sequentially combined to generate a luminescent signal that is > 3 times brighter than the standard 1 step protocol, within a shorter amount of time. DAF platform processes droplets on a rewritable fluidic carrier without cross-contamination or surface-degradation, allowing for the ability to execute reactions on overlapping fluidic paths, the potential to scale to massive interaction matrices within a small area, and the capability to perform successive experiments on a single, miniaturized device.

Advantages

- Contamination-free (< 10-10 % diffusion into carrier oil).
- Bio-compatible (> 99.2 % cell viability).

 Duke File (IDF) #

T-005408

 Inventor(s)

- Huang, Jun "Tony"
- Zhang, Peiran "Peiran"

 Links

- [From the lab of Dr. Tony Jun Huang](#)

 College

Pratt School of Engineering

**For more information
please contact**

Koi, Bethany
919-681-7552
bethany.koi@duke.edu

- Compact, durable, programmable, and rewritable.

Publications

- [Digital Acoustofluidics Enables Contactless and Programmable Liquid Handling \(Nature Communications, 2018\)](#)